












# Downdraft Station

Advanced protection  
against harmful chemicals  
and particulate

## Space-Saving Air Purification System with Containment Hood

### AVAILABLE FILTERS & ACCESSORIES

		
AG149 Filter Bag	AG259-2 Filter Bag	F022 2" HEPA Filter
		
F045-GPC 1" Carbon Filter	F033-GPC 2" Carbon Filter	F357 6" HEPA Filter
		
F007 2" Pre-Filter	F016 6" Hi-Cap Filter	H250 Silencer

Powered by a brushless motor and a multi-stage filtration system, the DDS Downdraft Station is capable of removing harmful particles and gases from the work area and helps you maintain a clean and healthy workplace.

Ideal for a wide range of applications\*, including chemical fume control, powder & dust removal, solvent vapor control, pharmaceutical powder filling, light grinding, acid gas fumes, anesthesia gas containment, epoxy fume control, touch-up paint applications or other coatings, and many more.

#### Basic Filter Configuration (#1-0031-0091):

- 2" Pre-filter, #F007-BX (8-pack)
- 6" HEPA filter (99.995% @ 0.3µm), #F357

#### SPECIFICATIONS

Air Flow: Nominal 600 CFM  
 Dimensions: Overall - 46.5 x 24 x 20 in, 150 lbs  
 (HxWxD) Cabinet - 24 x 29 x 20 in  
 Voltage: 120V / 60 Hz / 10A  
 Air Intake: 8.5"x17" (top grille, downdraft)  
 Blower Type: Direct Drive, 1/2 HP motor

#### INCLUDED



Foot-Pedal (AA114)

**1-800-626-0664**  
[airpurifiers-r-us.com](http://airpurifiers-r-us.com)

\* Quatro products are NOT INTENDED for use with explosive or flammable substances or environments.